

# Eaton BRP30L200R

Catalog Number: BRP30L200R

Eaton Eaton BR main lug loadcenter, Main lug only, 200 A, X5, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 60 Circuits, Single-pole, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BRP30L200R
<b>UPC</b>	<b>Product Length/Depth</b>
786689059354	3.88 in
<b>Product Height</b>	<b>Product Width</b>
29.13 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
19 lb	10 year
<b>Certifications</b>	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

60

### Number Of Poles

Single-pole

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Box size

X5

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### NEMA rating

NEMA 3R

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP30L200R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)