

# Eaton BRP30N200RG

Catalog Number: BRP30N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X6, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 60 Circuits, Single-pole, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



## General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP30N200RG
UPC	Product Length/Depth
786689059385	3.88 in
Product Height	Product Width
34.13 in	14.31 in
Product Weight	Warranty
22 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

Ground bar

### Type

Convertible

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

60

### Number Of Poles

Single-pole

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X6

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP30N200RG](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)