

Eaton BRP40B200R

Catalog Number: BRP40B200R

Plug-on neutral main circuit breaker
loadcenter,200A,X8,Aluminum,Cover included,NEMA
3R,Metallic,10 kAIC,BR,80 circuits,Single pole,40 spaces,Three-
wire,Single-phase,Combination,NEMA 3R,Type BR 1-inch
breakers,120/240V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP40B200R
UPC	Product Length/Depth
786689059408	39 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Drawings

[BR 1 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH M](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP40B200R](#)

NEMA rating
NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia