

Eaton BRP40B200V25

Catalog Number: BRP40B200V25

Value pack, Plug-on neutral main circuit breaker loadcenter, 200A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 80 circuits, Single pole, 40 spaces, Two hots, a neutral, and a ground, Single-phase, #6-2/0 AWG Cu/Al, Combination, NEMA 1, Type



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP40B200V25
UPC	Product Length/Depth
786689055288	39 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
36.4 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Value pack

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Wire size

#6-2/0 AWG Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 1

Enclosure material

Metallic

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP40B200V25](#)

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia