

Eaton BRP40BC200

Catalog Number: BRP40BC200

Plug-on neutral main circuit breaker loadcenter,200A,X8,Copper,Cover included,NEMA 1,Metallic,25kAIC,CSR2200,80 circuits,Single pole,40 spaces,Two hots, a neutral, and a ground,Single-phase,Gray,Combination,NEMA 1,Type BR 1-inch breakers,12



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP40BC200
UPC	Product Length/Depth
786689052973	39 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
37.5 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Copper

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Accessories

copper bus

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 1

Enclosure material

Metallic

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP40BC200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia