

Eaton BRP40N200

Catalog Number: BRP40N200

Eaton BR convertible loadcenter, Ground bar, includes BREQS125 hold-down screw, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 80 Circuits, Single-pole, 40 Spaces, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

| | |
|---------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR convertible loadcenter | BRP40N200 |
| UPC | Product Length/Depth |
| 786689044077 | 39 in |
| Product Height | Product Width |
| 3.88 in | 14.13 in |
| Product Weight | Warranty |
| 27 lb | 10 year |

Certifications

UL 67
UL 50

Product specifications

Special features

Ground bar, includes BREQS125 hold-down screw

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRP40N200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP40N200

Catalog Number: BRP40N200

Eaton BR convertible loadcenter, Ground bar, includes BREQS125 hold-down screw, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 80 Circuits, Single-pole, 40 Spaces, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

| | |
|---------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR convertible loadcenter | BRP40N200 |
| UPC | Product Length/Depth |
| 786689044077 | 39 in |
| Product Height | Product Width |
| 3.88 in | 14.13 in |
| Product Weight | Warranty |
| 27 lb | 10 year |
| Certifications | |
| UL 67 | |
| UL 50 | |

Product specifications

Special features

Ground bar, includes BREQS125 hold-down screw

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRP40N200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)