

Eaton BRP40N200G

Catalog Number: BRP40N200G

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 80 Circuits, Single-pole, 40 Spaces, Two hots, neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP40N200G
UPC	Product Length/Depth
786689053048	39 in
Product Height	Product Width
3.88 in	14.13 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 50 UL 67	



Product specifications

Number of spaces

40

Special features

Ground bar

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Main circuit breaker

CSR

Enclosure

NEMA 1

Amperage Rating

200 A

Number Of Poles

Single-pole

Mounting

Combination

Enclosure material

Metallic

Type

Convertible

Cover

Cover included

Used with

Type BR 1-inch breakers

Number of wires

Two hots, neutral and ground

Number of circuits

80

Voltage rating

120/240 V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP40N200G](#)

Box size

X8



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)