

Eaton BRP40N200R

Catalog Number: BRP40N200R

Eaton BR convertible loadcenter, Convertible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Single-pole, 40 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP40N200R
UPC	Product Length/Depth
786689059057	3.88 in
Product Height	Product Width
3.88 in	14.13 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP40N200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP40N200R

Catalog Number: BRP40N200R

Eaton BR convertible loadcenter, Convertible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Single-pole, 40 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP40N200R
UPC	Product Length/Depth
786689059057	3.88 in
Product Height	Product Width
3.88 in	14.13 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP40N200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)