

# Specifications



Photo is representative



## Eaton BRP40N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Single-pole, 40 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V

### General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP40N200RG
UPC	786689059064
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.13 in
PRODUCT WEIGHT	27 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	Ground bar
<b>TYPE</b>	Convertible
<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	BR
<b>MOUNTING</b>	Combination
<b>NUMBER OF CIRCUITS</b>	80
<b>NUMBER OF POLES</b>	Single-pole
<b>NUMBER OF SPACES</b>	40
<b>PHASE</b>	Single-phase
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>BOX SIZE</b>	X8
<b>ENCLOSURE</b>	NEMA 3R
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	10 kAIC
<b>NUMBER OF WIRES</b>	3

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP40N200RG](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.