

# Specifications



## Eaton BRP42LC225G

Eaton Eaton BR main lug loadcenter, Main Lug Only, Ground bar, 225 A, X8, Copper, Gray, NEMA 1, 10kAIC, BR, Surface, flush, 84 Circuits, 42 Spaces, Single-phase, 120/240V, #1-300kcmil

### General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP42LC225G
UPC	786689055059
PRODUCT LENGTH/DEPTH	39 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	36.3 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

## Product specifications

SPECIAL FEATURES	Main Lug Only
TYPE	Main Lug Only
AMPERAGE RATING	225 A
BUS MATERIAL	Copper
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	84
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	42
PHASE	Single-phase
USED WITH	BR
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil
BOX SIZE	X8
COLOR	Gray
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 1
NUMBER OF WIRES	Two hots, neutral and ground
QUANTITY	1

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRP42LC225G</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton BRP42LC225G

Eaton Eaton BR main lug loadcenter, Main Lug Only, Ground bar, 225 A, X8, Copper, Gray, NEMA 1, 10kAIC, BR, Surface, flush, 84 Circuits, 42 Spaces, Single-phase, 120/240V, #1-300kcmil

### General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP42LC225G
UPC	786689055059
PRODUCT LENGTH/DEPTH	39 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	36.3 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

## Product specifications

SPECIAL FEATURES	Main Lug Only
TYPE	Main Lug Only
AMPERAGE RATING	225 A
BUS MATERIAL	Copper
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	84
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	42
PHASE	Single-phase
USED WITH	BR
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil
BOX SIZE	X8
COLOR	Gray
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 1
NUMBER OF WIRES	Two hots, neutral and ground
QUANTITY	1

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRP42LC225G</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

