

# Eaton BRP60B200R

Catalog Number: BRP60B200R

Plug-on neutral main circuit breaker loadcenter,200A,X10,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,120 circuits,Single pole,60 spaces,Three-wire,Single-phase,Combination,NEMA 3R,Type BR 1-inch breakers,120/240V



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP60B200R
<b>UPC</b>	<b>Product Length/Depth</b>
786689059088	48.75 in
<b>Product Height</b>	<b>Product Width</b>
5.5 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
35 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## Product specifications

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

120

### Number Of Poles

Single-pole

### Number of spaces

60

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X10

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP60B200R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 3R

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRP60B200R

Catalog Number: BRP60B200R

Plug-on neutral main circuit breaker loadcenter,200A,X10,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,120 circuits,Single pole,60 spaces,Three-wire,Single-phase,Combination,NEMA 3R,Type BR 1-inch breakers,120/240V




Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP60B200R
<b>UPC</b>	<b>Product Length/Depth</b>
786689059088	48.75 in
<b>Product Height</b>	<b>Product Width</b>
5.5 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
35 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## Product specifications

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

120

### Number Of Poles

Single-pole

### Number of spaces

60

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X10

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP60B200R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 3R

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)