

Eaton BRSUR4040B200

Catalog Number: BRSUR4040B200

Eaton BR surge loadcenter, Factory integrated surge, Main circuit breaker, 200 A, L2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 40/40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR surge loadcenter	BRSUR4040B200
UPC	Product Length/Depth
782116417148	3.88 in
Product Height	Product Width
45 in	14.31 in
Product Weight	Warranty
45 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Special features

Factory integrated surge

Type

Main circuit breaker

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Mounting

Combination

Number of circuits

40

Number of spaces

40

Phase

Single-phase

Voltage rating

120/240 V

Box size

L2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Specifications and datasheets

Eaton Specification Sheet - BRSUR4040B200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRSUR4040B200

Catalog Number: BRSUR4040B200

Eaton BR surge loadcenter, Factory integrated surge, Main circuit breaker, 200 A, L2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 40/40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR surge loadcenter	BRSUR4040B200
UPC	Product Length/Depth
782116417148	3.88 in
Product Height	Product Width
45 in	14.31 in
Product Weight	Warranty
45 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Special features

Factory integrated surge

Type

Main circuit breaker

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Mounting

Combination

Number of circuits

40

Number of spaces

40

Phase

Single-phase

Voltage rating

120/240 V

Box size

L2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Specifications and datasheets

Eaton Specification Sheet - BRSUR4040B200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)