

Specifications



Eaton BRSUR4040B200

Eaton BR surge loadcenter, Factory integrated surge, Main circuit breaker, 200 A, L2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 40/40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V

General specifications

PRODUCT NAME	Eaton BR surge loadcenter
CATALOG NUMBER	BRSUR4040B200
UPC	782116417148
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	45 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	45 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Factory integrated surge
TYPE	Main circuit breaker
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
MOUNTING	Combination
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	40
PHASE	Single-phase
VOLTAGE RATING	120/240 V
BOX SIZE	L2
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRSUR4040B200
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

