

Eaton BRX2100

Catalog Number: BRX2100

Eaton BR thermal magnetic circuit breaker, Thermal-magnetic circuit breaker, 100 A, 65 kAIC, Two-pole, 120/240V, BRX, #14-2/0 AWG, BRX, 65 kAIC, 50-60 Hz



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BRX2100
	UPC
	786685926803
Product Length/Depth	Product Height
2.48 in	2.938 in
Product Width	Product Weight
2 in	0.76 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL Listed file E7819

Type

Thermal-magnetic circuit breaker

Amperage Rating

100 A

Voltage rating

120/240 V

Circuit breaker type

BR

Frequency rating

50-60 Hz

Capacity

65 kAIC

Interrupt rating

65 kAIC

Main circuit breaker

BR

Wire size

#14-2/0 AWG

Number of poles

Two-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Type BRX thermal-magnetic circuit breaker](#)

[Eaton Specification Sheet - BRX2100](#)