

# Eaton BRX2125

Catalog Number: BRX2125

Eaton BR thermal magnetic circuit breaker, thermal-magnetic circuit breaker, 125 A, 65 kAIC, Two-pole, 120/240V, BRX, #14-2/0 AWG, BRX, 65 kAIC, 50-60 Hz



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BRX2125
	UPC
	786685926827
<b>Product Length/Depth</b>	<b>Product Height</b>
3 in	3 in
<b>Product Width</b>	<b>Product Weight</b>
2 in	0.5 lb
<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C375	UL Listed file E7819

## Type

thermal-magnetic circuit breaker

## Amperage Rating

125 A

## Voltage rating

120/240 V

## Circuit breaker type

BR

## Frequency rating

50-60 Hz

## Capacity

65 kAIC

## Interrupt rating

65 kAIC

## Main circuit breaker

BR

## Wire size

#14-2/0 AWG

## Number of poles

Two-pole

## Brochures

[Loadcenters and Circuit Breakers](#)

## Specifications and datasheets

[Eaton Specification Sheet - BRX2125](#)

[Type BRX thermal-magnetic circuit breaker](#)