



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BSV10Q Highland Vinyl Ins Butt Connector, 12-10awg *Minnesota Mining (3M)*

| | |
|------------------|---|
| Catalog Number | BSV10Q |
| Manufacturer | Minnesota Mining (3M) |
| Description | Butt Splice, #12 Awg Conductor Size, #10 Awg Conductor Size, Insulated, Vinyl Insulation Material, Copper Conductor Material, 600 V (Building Wiring);1000 V (Signs/Fixture), -40 °F Operating Temperature, +221 °F Operating Temperature, 1.02 In Overall Length, Butt Splice Terminal, 600 V, 0.15 LB |
| Weight per unit | 0.0148 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Descriptions

| | |
|------------------------|---|
| Description | HIGHLAND VINYL INS BUTT CONNECTER, 12-10AWG |
| extra long description | 3M 7000133654 3M™ Highland™ Vinyl I |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Scotchlok |
| GTIN | 00051128599969 |
| Manufacturers Part Number | 7000133654 |
| UPC | 051128599969 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | WIRE NUTS |
| Type | Butt Splice |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.0148 |

Uses, Certifications, and Standards

| | |
|----------|------------|
| standard | UL and CSA |
|----------|------------|