



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BSV10Q Highland Vinyl Ins Butt Connector, 12-10awg *Minnesota Mining (3M)*

|                  |   |
|------------------|---|
| Catalog Number   | BSV10Q  |
| Manufacturer     | Minnesota Mining (3M)   |
| Description      | Butt Splice, #12 Awg Conductor Size, #10 Awg Conductor Size, Insulated, Vinyl Insulation Material, Copper Conductor Material, 600 V (Building Wiring);1000 V (Signs/Fixture), -40 °F Operating Temperature, +221 °F Operating Temperature, 1.02 In Overall Length, Butt Splice Terminal, 600 V, 0.15 LB |
| Weight per unit  | 0.0148 (lbs/each)   |
| Product Category | Small Terminals & Connectors  |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | HIGHLAND VINYL INS BUTT CONNECTER, 12-10AWG |
| extra long description | 3M 7000133654 3M™ Highland™ Vinyl I         |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Scotchlok      |
| GTIN                      | 00051128599969 |
| Manufacturers Part Number | 7000133654     |
| UPC                       | 051128599969   |

### Taxonomies, Classifications, and Categories

|                      |             |
|----------------------|-------------|
| Category Description | WIRE NUTS   |
| Type                 | Butt Splice |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 10     |
| Weight Per each | 0.0148 |

### Uses, Certifications, and Standards

|          |            |
|----------|------------|
| standard | UL and CSA |
|----------|------------|