



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

BT3IC 11.3" NylN CBL Tie SS Barb Int Cross Sec WHT *Panduit Corporation*

Catalog Number	BT3IC
Manufacturer	Panduit Corporation
Description	The BT3I-C Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless-Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Intermediate Cross Section, 11.3" (287MM) Length. Appropriate For Indoor Use, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 100.
Weight per unit	0.3850 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	40

Dimensions and Weight

Length	11.3
Thickness	0.05

Descriptions

Description	11.3" NYL N CBL TIE SS BARB INT CROSS SEC WHT
extra long description	PAN BT3I-C Dome-Top® BT3I-C Barb Ti
Long Description	The BT3I-C Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Intermediate cross section, 11.3" (287mm) length. Appropriate for Indoor use, made of Nylon 6.6, are natural in color and come in packages of 100.
Product Type	Dome-Top® BT3I-C Barb Tie, PA6.6, 11.3"L, 40LB, PK100
Special Features	Indoor

Manufacturer Information

Brand	PANDUIT
GTIN	00074983413669
Manufacturers Part Number	BT3I-C
UPC	074983413669

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 100

Packaging

Carton 100

Package 1000

Weight Per each 0.385

Uses, Certifications, and Standards

standard UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC
10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant