

# Eaton C0050E3A

Catalog Number: C0050E3A

Eaton Type MTE industrial control transformer, pv: 208/277v, taps: none, sv: 120v, 55°c, 50 va

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type MTE industrial control transformer	C0050E3A

<b>UPC</b>
786680550003

<b>Product Length/Depth</b>	<b>Product Height</b>
3.61 in	3.26 in

<b>Product Width</b>	<b>Product Weight</b>
3 in	2.8 lb

<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the	

Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Certifications**  
 UL Listed  
 CSA Certified  
 cUL Certified

## Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

## Physical Attributes

Coil material  
Copper windings

Design  
MTE

Tap size  
None

## Performance Ratings

Primary voltage  
208/277 V

Temperature rating  
55°C

Volt ampere rating  
50 VA

Secondary voltage  
120 V

## Resources

[Specifications and datasheets](#)

[Eaton Specification Sheet - C0050E3A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)