



Powering Business Worldwide

pe.eaton.com

Eaton Industrial Control Transformer

C0100E2AFB

UPC:786680420849

Dimensions:

- **Height:** 4.252 IN
- **Length:** 3.386 IN
- **Width:** 3.386 IN

Weight:4.4 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 240 X 480V, 230 X 460V, 220 X 440V
- **Secondary Voltage:** 120/115/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 100 VA

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)



- [MTE Control Transformer 100 VA Series 2 - C0100E2AFB](#)
- [Eaton Specification Sheet - C0100E2AFB](#)

Certifications:

- UL Listed
- cUL Certified
- CSA Certified

Product compliance:

- RoHS Compliant



Powering Business Worldwide

pe.eaton.com

Eaton Industrial Control Transformer

C0100E2AFB

UPC:786680420849

Dimensions:

- **Height:** 4.252 IN
- **Length:** 3.386 IN
- **Width:** 3.386 IN

Weight:4.4 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 240 X 480V, 230 X 460V, 220 X 440V
- **Secondary Voltage:** 120/115/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 100 VA

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)



- [MTE Control Transformer 100 VA Series 2 - C0100E2AFB](#)
- [Eaton Specification Sheet - C0100E2AFB](#)

Certifications:

- UL Listed
- cUL Certified
- CSA Certified

Product compliance:

- RoHS Compliant