

Eaton C0250E6U

Catalog Number: C0250E6U

Eaton Type MTE industrial control transformer, pv:
240/416/480/600v, 230/400/460/575v, 220/380/440/550v,
208/500v, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v,
85/100/110v, 55°C, 250 va

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0250E6U
	UPC
	786680019135

Product Length/Depth	Product Height
5.866 in	3.819 in

Product Width	Product Weight
4.488 in	14.7 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	cUL Certified
	UL Listed
	CSA Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

208/500 V, 220/380/440/550 V, 230/400/460/575 V,
240/416/480/600 V

Temperature rating

55°C

Volt ampere rating

250 VA

Secondary voltage

99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0250E6U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C0250E6U

Catalog Number: C0250E6U

Eaton Type MTE industrial control transformer, pv:
240/416/480/600v, 230/400/460/575v, 220/380/440/550v,
208/500v, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v,
85/100/110v, 55°C, 250 va

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0250E6U
	UPC
	786680019135

Product Length/Depth	Product Height
5.866 in	3.819 in

Product Width	Product Weight
4.488 in	14.7 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	cUL Certified
	UL Listed
	CSA Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

208/500 V, 220/380/440/550 V, 230/400/460/575 V,
240/416/480/600 V

Temperature rating

55°C

Volt ampere rating

250 VA

Secondary voltage

99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0250E6U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)