



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C0300E1B 300 Va Type Mte Control Transformer

Eaton Corp

Catalog Number	C0300E1B
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 120 X 240V, Taps: None, SV: 24V, 55°C, 300 Va
Weight per unit	8.0 (lbs/each)
Product Category	Encapsulated Industrial Contro

### Features

dimensions	4.5600 IN X 4.5000 IN X 4.2200 IN
kva rating	300 VA
Primary Voltage	120 x 240 V
Secondary Voltage	24 V
Tap Size	NONE

### Descriptions

Description	300 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C0300E1B 300 VA Type MTE Contro
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 120 x 240v, taps: none, sv: 24v, 55°C, 300 va
Product Type	300 Va Type Mte Control Transformer

### Manufacturer Information

Brand	Eaton
GTIN	00786680423048
Manufacturers Part Number	C0300E1B
UPC	786680423048

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer

### Packaging

Carton	1
Weight Per each	8



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Other
standard	UL Listed, CSA Certified, cUL Certified, RoHS Compliant
Temperature Rating	55°C