



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C1000E2A 1000 Va Type Mte Control Transformer

*Eaton Corp*

Catalog Number	C1000E2A
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, SV: 120/115/110V, 55°C, 1000 Va
Weight per unit	34.0 (lbs/each)
Product Category	Core & Coil Industrial Control

### Features

dimensions	6.4570 IN X 6.7320 IN X 5.6690 IN
kva rating	1000 VA
Primary Voltage	220 X 440 V, 230 X 460 V, 240 X 480 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

### Descriptions

Description	1000 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C1000E2A 1000 VA Type MTE Contr
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°c, 1000 va
Product Type	1000 Va Type Mte Control Transformer

### Manufacturer Information

Brand	Eaton
GTIN	00786680125508
Manufacturers Part Number	C1000E2A
UPC	786680125508

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Weight Per each ..... 34

## Uses, Certifications, and Standards

Application ..... Other

standard ..... CSA Certified,cUL Certified,UL Listed,RoHS Compliant

Temperature Rating ..... 55°C