

# Eaton C25BNF240A

Catalog Number: C25BNF240A

Eaton definite purpose contactor, Quick, 30A, 24 Vac, 50/60 Hz, Open with metal mounting plate, Compact, two-pole, 30A, Contactor, Two-pole, 40A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing

## General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25BNF240A
UPC	Product Length/Depth
786685116150	2.32 in
Product Height	Product Width
3.19 in	1.97 in
Product Weight	Warranty
.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified



## Product specifications

### Frame size

Compact, two-pole

### Type

Non-reversing

### Inductive full load

40 A

### Model

Contactors

### Connection

Quick

### Enclosure

Open with metal mounting plate

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Amperage Rating

40A

### Resistive load

50 A

### Number Of Poles

Two-pole

### Coil

110-120 Vac, 50/60 Hz

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25BNF AutoCAD 2D Footprint \(mm\)](#)

[C25BNF 3D Inventor](#)

[C25BNF 2D Drawing Xchange](#)

[C25BNF AutoCAD 2D Footprint](#)

[C25BNF 3D Model Xchange](#)

[C25BNF 2D PDF](#)

### Specifications and datasheets

[Quick Selector - Definite Purpose Contactors](#)

[Eaton Specification Sheet - C25BNF240A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)