

# Eaton C25DND325A

Catalog Number: C25DND325A

Eaton definite purpose contactor, Quick, 25A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 25A, Contactor, Three-pole, 35A, Screw/pressure plate and quick connect terminal (side-by-side), Non-reversing

## General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25DND325A
UPC	Product Length/Depth
782116300501	3.35 in
Product Height	Product Width
2.5 in	2.4 in
Product Weight	Warranty
1 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified UL Recognized

## defaultTaxonomyAttributeLabel

### Amperage Rating

25A

### Number Of Poles

Three-pole

### Type

Non-reversing

### Coil

110-120 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

25 A

### Model

Contactors

### Resistive load

35 A

### Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25DND3 3D Inventor](#)

[C25DND3 2D Drawing Xchange](#)

[C25DND3 AutoCAD 2D Footprint \(mm\)](#)

[C25DND3 AutoCAD 2D Footprint](#)

[C25DND3 3D Model Xchange](#)

[C25DND3 2D PDF](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25DND325A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)