

Eaton C25DNF330A

Catalog Number: C25DNF330A

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 110/120 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

General specifications



Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF330A
UPC	Product Length/Depth
782116300594	3.35 in
Product Height	Product Width
3.75 in	2.4 in
Product Weight	Warranty
1.05 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

Product specifications

Amperage Rating

30A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

208-240 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactor

Resistive load

40 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Specifications and datasheets

[Eaton Specification Sheet - C25DNF330A](#)