

# Eaton C25DNF330C

Catalog Number: C25DNF330C

Eaton definite purpose contactor, Quick, 30A, 208-240 Vac at 50/60 Hz, Open with metal mounting plate, 15-50A, two- or 3P, 15-50A, two- and 3P, Contactor, 3P, Global ratings, Box lugs (posidrive setscrew) and quick connect terminals

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25DNF330C
<b>UPC</b>	<b>Product Length/Depth</b>
782116311361	3.35 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	2.4 in
<b>Product Weight</b>	<b>Warranty</b>
1.3 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)

## Product specifications

### Amperage Rating

30A

### Number Of Poles

Three-pole

### Options

Global listed

### Type

Non-reversing

### Auxiliary contacts

Quick connect (side-by-side)

### Coil

440-480 Vac, 50/60 Hz

### Coil voltage

277 Vac, 60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

30 A

### Model

Contactors

### Resistive load

40 A

### Series

D1

### Terminals

Box lugs (posidrive setscrew)

### Connection

Quick

## Resources

### Specifications and datasheets

Eaton Specification Sheet - C25DNF330C



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton C25DNF330C

Catalog Number: C25DNF330C

Eaton definite purpose contactor, Quick, 30A, 208-240 Vac at 50/60 Hz, Open with metal mounting plate, 15-50A, two- or 3P, 15-50A, two- and 3P, Contactor, 3P, Global ratings, Box lugs (posidrive setscrew) and quick connect terminals

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25DNF330C
<b>UPC</b>	<b>Product Length/Depth</b>
782116311361	3.35 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	2.4 in
<b>Product Weight</b>	<b>Warranty</b>
1.3 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)

## Product specifications

### Amperage Rating

30A

### Number Of Poles

Three-pole

### Options

Global listed

### Type

Non-reversing

### Auxiliary contacts

Quick connect (side-by-side)

### Coil

440-480 Vac, 50/60 Hz

### Coil voltage

277 Vac, 60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

30 A

### Model

Contactors

### Resistive load

40 A

### Series

D1

### Terminals

Box lugs (posidrive setscrew)

### Connection

Quick

## Resources

### Specifications and datasheets

Eaton Specification Sheet - C25DNF330C



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)