

# Eaton C25DNF330T

Catalog Number: C25DNF330T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 12 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25DNF330T
<b>UPC</b>	<b>Product Length/Depth</b>
782116311422	3.35 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	2.4 in
<b>Product Weight</b>	<b>Warranty</b>
1.19 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	CSA Certified
	UL Recognized
	UL Listed

## Product specifications

### Amperage Rating

30A

### Number Of Poles

Three-pole

### Type

Non-reversing

### Auxiliary contacts

Pressure plate and quick connect

### Coil

24 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

30 A

### Model

Contactors

### Resistive load

40 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Specifications and datasheets

Eaton Specification Sheet - C25DNF330T



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)