

# Eaton C25DNF340A

Catalog Number: C25DNF340A

Eaton definite purpose contactor, Quick, Class J, 600V, 60A, 40A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 40A, Contactor, 3P, 50A, Box lugs (posidrive setscrew) and quick connect terminals , Non-reversing



## General specifications

|                                  |                      |
|----------------------------------|----------------------|
| Product Name                     | Catalog Number       |
| Eaton definite purpose contactor | C25DNF340A           |
| UPC                              | Product Length/Depth |
| 782116300662                     | 3.35 in              |
| Product Height                   | Product Width        |
| 3.75 in                          | 2.4 in               |
| Product Weight                   | Warranty             |
| 0.9 lb                           | 1 year               |
| Compliances                      | Certifications       |
| RoHS Compliant                   | CSA Certified        |
|                                  | UL Recognized        |

## defaultTaxonomyAttributeLabel

### Amperage Rating

40A

### Number Of Poles

Three-pole

### Type

Non-reversing

### Coil

110-120 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

40 A

### Model

Contactors

### Resistive load

50 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25DNF3 3D Inventor](#)

[C25DNF3 AutoCAD 2D Footprint](#)

[C25DNF3 2D Drawing Xchange](#)

[C25DNF3 AutoCAD 2D Footprint \(mm\)](#)

[C25DNF3 3D Model Xchange](#)

[C25DNF3 2D PDF](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25DNF340A](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)