

Eaton C25DNF340C

Catalog Number: C25DNF340C

Eaton definite purpose contactor, Quick, 40A, 550-600 Vac, 50/50 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, Three-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals , Non-reversing



General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF340C
UPC	Product Length/Depth
782116311651	3.35 in
Product Height	Product Width
2.75 in	2.4 in
Product Weight	Warranty
1.2 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized
	UL Listed file E1491 (Guide Number NLDX2)

defaultTaxonomyAttributeLabel

Amperage Rating

40A

Number Of Poles

Three-pole

Options

Global listed

Type

Non-reversing

Auxiliary contacts

Quick connect (side-by-side)

Coil

440-480 Vac, 50/60 Hz

Coil voltage

550-600 Vac, 50 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactor

Resistive load

50 A

Series

D1

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

C25DNF3 2D Drawing Xchange

C25DNF3 3D Model Xchange

C25DNF3 AutoCAD 2D Footprint

C25DNF3 AutoCAD 2D Footprint (mm)

C25DNF3 2D PDF

C25DNF3 3D Inventor

Specifications and datasheets

Eaton Specification Sheet - C25DNF340C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)