

Eaton C25DNF340T

Catalog Number: C25DNF340T

Eaton definite purpose contactor, Quick, 40A, 24 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, 2 and 3 pole, 40A, Contactor, Three-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing



General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF340T
UPC	Product Length/Depth
782116300709	3.35 in
Product Height	Product Width
2.3 in	2.4 in
Product Weight	Warranty
1.05 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized

defaultTaxonomyAttributeLabel

Amperage Rating

40A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

24 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactor

Resistive load

50 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25DNF3 AutoCAD 2D Footprint](#)

[C25DNF3 AutoCAD 2D Footprint \(mm\)](#)

[C25DNF3 3D Model Xchange](#)

[C25DNF3 3D Inventor](#)

[C25DNF3 2D Drawing Xchange](#)

[C25DNF3 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DNF340T](#)