

Eaton C25ENF440T

Catalog Number: C25ENF440T

Eaton definite purpose contactor, Quick, 40A, 24 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, Four-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25ENF440T
UPC	Product Length/Depth
782113536613	3.38 in
Product Height	Product Width
3.75 in	2.68 in
Product Weight	Warranty
2.3 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

Catalog Notes

Resistive Load rating per pole

defaultTaxonomyAttributeLabel

Amperage Rating

40A

Number Of Poles

Four-pole

Type

Non-reversing

Coil

24 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactor

Resistive load

50 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25ENF4 3D Model Xchange](#)

[C25ENF4 3D Inventor](#)

[C25ENF4 2D Drawing Xchange](#)

[C25ENF4 AutoCAD 2D Footprint \(mm\)](#)

[C25ENF4 2D PDF](#)

[C25ENF4 AutoCAD 2D Footprint](#)

Specifications and datasheets

[Eaton Specification Sheet - C25ENF440T](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia