

# Eaton C25FNF260T

Catalog Number: C25FNF260T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect, 24 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Two-pole, Individual pkg, F1, Box lugs (posidrive setscrew), Non-reversing

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25FNF260T
<b>UPC</b>	<b>Product Length/Depth</b>
782113476124	3.97 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	2.63 in
<b>Product Weight</b>	<b>Warranty</b>
2.66 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	CSA Certified UL Recognized
<b>Catalog Notes</b>	
Resistive Load rating per pole	

## defaultTaxonomyAttributeLabel

### Amperage Rating

75A

### Number Of Poles

Two-pole

### Type

Non-reversing

### Coil

440-480 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

75 A

### Model

Contactor

### Resistive load

90 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25FNF2 3D Model Xchange](#)

[C25FNF2 3D Inventor](#)

[C25FNF2 2D PDF](#)

[C25FNF2 2D Drawing Xchange](#)

[C25FNF2 AutoCAD 2D Footprint \(mm\)](#)

[C25FNF2 AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25FNF260T](#)