

Eaton C25FNF360C

Catalog Number: C25FNF360C

Eaton definite purpose contactor, Quick, 60A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 60A, Contactor, Three-pole, 75A, Box lugs (posidrive setscrew) and quick connect terminals

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25FNF360C
UPC	Product Length/Depth
782113499956	3.97 in
Product Height	Product Width
3.75 in	2.63 in
Product Weight	Warranty
2.8 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified UL Recognized
Catalog Notes	
Resistive Load rating per pole	

defaultTaxonomyAttributeLabel

Amperage Rating

60A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

440-480 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

60 A

Model

Contactors

Resistive load

75 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25FNF3 AutoCAD 2D Footprint \(mm\)](#)

[C25FNF3 3D Model Xchange](#)

[C25FNF3 3D Inventor](#)

[C25FNF3 AutoCAD 2D Footprint](#)

[C25FNF3 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - C25FNF360C](#)