

Eaton C440B1A100SAX

Catalog Number: C440B1A100SAX

Eaton C440 electronic overload relay, C440 Electronic Overload Relay - NEMA, Separate Mount, 55mm frame, Selectable 10A, Class 10 ,20, 30, Overload 20-100A, Standard



General specifications

Product Name

Eaton C440 electronic overload relay

Catalog Number

C440B1A100SAX

UPC

786685412429

Product Length/Depth

5.52 in

Product Height

4.13 in

Product Width

2.21 in

Product Weight

0.87 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked

Certifications

CSA Certified
UL Listed

defaultTaxonomyAttributeLabel

Overload range

20-100A

Special features

Standard

Type

Electronic overload relay

Frame size

55 mm

Rated short-time withstand current (Icw)

Manual

Auto

Trip type

Selectable 10 A, class 10 ,20, 30

Size

Separate Mount

Resources

Brochures

C440 Electronic Overload Relay

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

C440B_AX AutoCAD 2D Footprint (mm)

C440B_AX 2D Drawing Xchange

C440B_AX AutoCAD 2D Footprint

C440B_AX 3D Inventor

C440B_AX 2D PDF

C440B_AX 3D Model Xchange

Installation instructions

C440 NEMA Electronic Overload - Self Powered

Specifications and datasheets

Eaton Specification Sheet - C440B1A100SAX



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia