



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C440C1A140SAX C440 OI 28-140A Standalone STD FLT *Eaton Corp*

Catalog Number	C440C1A140SAX
Manufacturer	Eaton Corp
Description	Eaton C440 Electronic Overload Relay, C440 Electronic Overload Relay - Nema, Separate Mount, 110MM Frame, Selectable 10A, Class 10 , 20, 30, Overload 24-140A, Standard
Weight per unit	5.0 (lbs/each)
Product Category	Overload Relays & Accessories

Features

dimensions	6.2000 IN X 4.3300 IN X 6.0000 IN
Trip Type	Selectable 10 A, class 10 ,20, 30

Dimensions and Weight

Size	Separate Mount
------	----------------

Descriptions

Description	C440 OL 28-140A STANDALONE STD FLT
extra long description	ETN C440C1A140SAX C440 OL (28-140A)
Features	The C440/XTOE electronic overload relay delivers enhanced motor protection and communications capabilities in a single compact device, directly monitoring motor current in each phase. Thermal modeling is performed electronically with precision solid-state components.
Long Description	Eaton C440 electronic overload relay, C440 Electronic Overload Relay - NEMA, Separate Mount, 110mm frame, Selectable 10A, Class 10 ,20, 30, Overload 24-140A, Standard
Product Type	C440 OI (28-140A) Standalone STD FLT
Special Features	Standard

Manufacturer Information

Brand	Eaton
GTIN	00786685533421
Manufacturers Part Number	C440C1A140SAX
UPC	786685533421

Taxonomies, Classifications, and Categories

Type	Electronic overload relay
------	---------------------------

Packaging

Carton	1
Weight Per each	5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

UL Listed, CSA Certified, CE Marked