



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C8N 8AWG Closed End Wire Nyl Conn W/CRMP SLV

Nsi Industries

Catalog Number	C8N
Manufacturer	Nsi Industries
Description	The Easy-Twist C8-N 40-Count Pack Of Nylon Closed-End Wire Connectors Are Designed For Use On Pre-Insulated Wires In The 16-10 Awg Size Range. Theyâ€™re UI-Certified As Self-Extinguishing and Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Closed-End Nylon Connector Features An Internal Metal Crimp Sleeve That Can Be Tightened Over Twisted Pre-Insulated Wires to Form A Safe and Secure Join. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to
Weight per unit	N/A
Product Category	Tools & Testers

Features

insulation	Nylon 66
Material	Nylon
Number of Conductors	1
Poles	1
Voltage Rating	300 V
Warranty	1 YEAR
Wire Size	16-10 AWG
Wire Type	CU Wire Only

Material, Color, and Finish

Color	White
Finish	NYLON

Dimensions and Weight

Size	H=1.09 - W=.563 -ID=.209
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	8AWG CLOSED END WIRE NYL CONN W/CRMP SLV
extra long description	NSI C8-N Easy Twist Closed End Conn
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These closed-end connectors feature a corrosion and chemical resistant nylon cover over a metal crimp cap wire terminal. These connectors are easy to install; simply twist your wires together to form a connection, then slide the closed end butt connector over the pigtail and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these closed-end conn
Long Description	The Easy-Twist C8-N 40-Count Pack of Nylon Closed-End Wire Connectors are designed for use on pre-insulated wires in the 16-10 AWG size range. They are UL-certified as self-extinguishing and rated for a maximum temperature of 105°C (221°F). The closed-end nylon connector features an internal metal crimp sleeve that can be tightened over twisted pre-insulated wires to form a safe and secure join. Their compact design is useful for applications in tight areas or anywhere else you need to
Product Type	Easy Twist Closed End Conn 16-10 40 PK
Special Features	16-10 AWG - UL94 V-2 - Made From Nylon 66 - 40 Pcs Blister

Manufacturer Information

Brand	NSI
GTIN	00662381362094
Manufacturers Part Number	C8-N
UPC	662381362094

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Closed End Connectors

Availability

minimum qty	30
-------------	----

Packaging

Carton	30
Weight Per each	0

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C
Temperature Rating	105 C