



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CC3150 CC BRKR 150A/3 Pole 240V 10K

Eaton Corp

Catalog Number	CC3150
Manufacturer	Eaton Corp
Description	Type CC Molded Case Circuit Breaker, Three-Pole, 150A, 240V, 10 Kaic, #4-4/0 Awg Cu/Al 60°C or 75°C
Weight per unit	2.9 (lbs/each)
Product Category	3 Pole Base Mount Circuit Brea

Features

dimensions	8.0000 IN X 7.0000 IN X 5.2500 IN
interrupt rating	10 kAIC
Poles	Three-pole
Voltage Rating	240 V - 240 V

Descriptions

Description	CC BRKR 150A/3 POLE 240V 10K
extra long description	ETN CC3150 CC Breaker 150A/3 Pole 2
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Type CC Molded Case Circuit Breaker, Three-Pole, 150A, 240V, 10 kAIC, #4-4/0 AWG Cu/Al 60°C or 75°C
Product Type	CC Breaker 150A/3 Pole 240V 10K

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113266626
Manufacturers Part Number	CC3150
UPC	782113266626

Taxonomies, Classifications, and Categories

Category Description	Breaker Enclosures with or without Breaker
Type	Accessory

Packaging

Carton	1
Weight Per each	2.9



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other
Generation - Conventional Energy - Conventional
Energy
Datacenters - IT Space: CI and Hyper
Converged
Other
Residential Bldgs & Facilities - Residential Bldgs
& Facilities - Other

standard

UL 489, Contact Manufacturer