



Powering Business Worldwide

pe.eaton.com

Type CCV Tenant Main Circuit Breaker

CCV2125

UPC:786685368399

Dimensions:

- **Height:** 5.4 IN
- **Length:** 7.7 IN
- **Width:** 4.5 IN

Weight:2.9 LB

Notes:Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Amperage Rating:** 125A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CCV
- **Wire Size:** #2/0 AWG-300 kcmil Cu/Al
- **Used With:** Type ECC Unit Enclosures

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CCV2125](#)

Certifications:

- UL 489

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Type CCV Tenant Main Circuit Breaker

CCV2125

UPC:786685368399

Dimensions:

- **Height:** 5.4 IN
- **Length:** 7.7 IN
- **Width:** 4.5 IN

Weight:2.9 LB

Notes:Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Amperage Rating:** 125A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CCV
- **Wire Size:** #2/0 AWG-300 kcmil Cu/Al
- **Used With:** Type ECC Unit Enclosures

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CCV2125](#)

Certifications:

- UL 489

Product compliance: No Data

