

# Eaton CCV2125

Catalog Number: CCV2125

Eaton Type CCV Tenant Main Circuit Breaker, Tenant main circuit breaker, 125 A, 10 kAIC, Two-pole, 120/240 V, #2/0 AWG-300 kcmil Cu/Al, CCV, Type ECC unit enclosures

## General specifications



### Product Name

Eaton CCV tenant main breaker

### Catalog Number

CCV2125

### UPC

786685368399

### Product Length/Depth

7.7 in

### Product Height

5.4 in

### Product Width

4.5 in

### Product Weight

2.9 lb

### Warranty

Limited lifetime residential, 1 year commercial

### Certifications

UL 489

### Catalog Notes

Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.



Powering Business Worldwide

## Type

Tenant main circuit breaker

## Amperage Rating

125 A

## Voltage rating

120/240 V

## Circuit breaker frame type

CCV

## Used with

Type ECC Unit Enclosures

## Interrupt rating

10 kAIC

## Main circuit breaker

CCV

## Wire size

#2/0 AWG-300 kcmil Cu/Al

## Number of poles

Two-pole

## Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

## Specifications and datasheets

[Eaton Specification Sheet - CCV2125](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)