


While we've spent a long time perfecting an insulating coating, we are continuously developing new technologies to improve safety, durability, and usability. This pursuit is evident in our Composite Driver Tools. By eliminating 95% of all conductive material and utilizing cutting edge technology, we have created drivers that are strong, light-weight, durable, and most importantly, safe.



Screwdrivers




PN	DESC
CM2-3.....	1/8" X 3"
CM2-6.....	1/8" X 6"
CMC5-CG....	3/16" X 5"
CMC6-CG....	3/16" X 6"
CM4-CG.....	1/4" X 4-1/2"
CM6-CGC....	1/4" X 6"

- Comply with ASTM F1505 and IEC 60900 Standards and help meet the requirements of OSHA 1910.331-335, NFPA 70E®, and CSA-Z462
- Tested to 10,000 VAC and Rated for 1,000 VAC when working on or around energized parts
- Slender Shape at Tip
- Cushion Grip (CG) handle for greater comfort and torque
- Internal Flanges in handle provide solid, twist-resistant blade



CM6-CGC



PN	DESC
C516-6CG.....	5/16" X 6"
CM516-6CG...	5/16" X 6"
C38-6CG.....	3/8" X 6"

Nut Drivers

PN	DESC
CP1-3-CG...#1 X 3"	
CP1-5CG...#1 X 5"	
CP2-4CG...#2 X 4"	
CP2-6CG...#2 X 6"	
CP3-6CG...#3 X 6"	

PN	DESC
CR1-6CG....#1 X 6"	
CR2-6CG...#2 X 6"	
CR3-6CG...#3 X 6"	


PN	DESC
CND316-CG3... 3/16" X 3"	
CND316-CG.....3/16" X 6"	
CND140-CG3... 1/4" X 3"	
CND140-CG.....1/4" X 6"	
CND516-CG3... 5/16" X 3"	
CND516-CG.....5/16" X 6"	
CND1132-CG3.. 11/32" X 3"	
CND1132-CG.....11/32" X 6"	
CND380-CG3.. 3/8" X 3"	
CND380-CG.... 3/8" X 6"	
CND716-CG3.... 7/16" X 3"	
CND716-CG..... 7/16" X 6"	
CND120-CG3... 1/2" X 3"	
CND120-CG.....1/2" X 6"	
CND916-CG3... 9/16" X 3"	
CND916-CG.....9/16" X 6"	
CND580-CG....5/8" X 6"	



CR1-6CG



CP2-4CG



CND916-CG



CM2-3



CMTS-6

Magnetic Tip Multi-Bit Drivers

PN	DESC
CMTS-6.....	6" Shaft, 3/16" & 1/4" Cabinet, #1, #2 & #3 Phillips
CMTS-6CA..	6" Shaft, 3/16" & 1/4" Cabinet, #2 & #3 Phillips, #2 Robertson



Sets / Rolls

TR-5CSD

Composite Cabinet Tip Screwdrivers - 3/16" X 6", 1/4" X 6", 3/8" X 6"
 Composite Phillips Tip Screwdrivers - #2 X 6", #3 X 6"
 Driver Roll Pouch 6

TR-6SD-C

Composite Cabinet Tip Screwdrivers - 3/16" X 5", 3/16" X 6", 1/4" X 6"
 Composite Mechanics Tip Screwdriver - 5/16" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 3", #2 X 4"
 Driver Roll Pouch 6

TR-6CSD

Composite Cabinet Tip Screwdrivers - 1/8" X 6", 3/16" X 6", 1/4" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 5", #2 X 6", #3 X 6"
 Driver Roll Pouch 6

TR-6SD-CSO

Composite Cabinet Tip Screwdrivers - 3/16" X 6", 1/4" X 6"
 Composite Mechanics Tip Screwdriver - 5/16" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 5", #2 X 6", #3 X 6"
 Driver Roll Pouch 6

TR-8SD-C

Composite Cabinet Tip Screwdrivers - 3/16" X 5", 3/16" X 6", 1/4" X 4-1/2",
 1/4" X 6"
 Composite Mechanics Tip Screwdriver - 5/16" X 6", 3/8" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 3", #2 X 4"
 Driver Roll Pouch 8

TR-6NDXL-C

6" Composite Nut Drivers - 3/16", 1/4", 5/16", 3/8", 7/16", 1/2"
 Driver Roll Pouch 6

TR-8CND

6" Composite Nut Drivers - 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16"
 Driver Roll Pouch 8

TR-8NDXL-C

6" Composite Nut Drivers: 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2"
 Composite Holding Nut Starter: 5/16" X 8"
 Driver Roll Pouch 8



Holding Screw and Nut Starters

- Spring-Loaded Design allows for easy operation while wearing insulating gloves
- Slender Design for tight area access and storage
- Includes opposing end magnet for retrieval
- Available in multiple sizes and bit tip configurations

PN _____ DESC _____
 CD3-8.....8" Flat Tip
 CD11-8..... 8" Phillips Tip
 CDNS-8...8" Nut Starter

CD11-8



Fuse Pullers




PFP-1

PN _____ DESC _____
 PFP-0..... 5" Fuse Puller without Guards
 PFP-0G.....7-1/4" Fuse Puller with Guards
 PFP-1.....7-1/2" Fuse Puller (without Guards)
 PFP-2G.....5" Fuse Puller with Guards
 PFP-3.....11-3/4" Fuse Puller without Guards

Non-Conductive Pliers

- Non-conductive tool
- Completely concealed pivot pin (only steel component)
- Slender Jaws for entry to tight areas

PN _____ DESC _____
 PK100....7" Fiberglass Reinforced Plastic



PK100



Measuring Tape

PN _____ DESC _____
 CTM-33... 33' Fully Non-Conductive
 Fiberglass Measuring Tape


609.387.1040 • 800.654.1292 • fax: 609.386.8885

www.cementexusa.com • orders@cementexusa.com • rfq@cementexusa.com

While we've spent a long time perfecting an insulating coating, we are continuously developing new technologies to improve safety, durability, and usability. This pursuit is evident in our Composite Driver Tools. By eliminating 95% of all conductive material and utilizing cutting edge technology, we have created drivers that are strong, light-weight, durable, and most importantly, safe.



Screwdrivers




PN	DESC
CM2-3.....	1/8" X 3"
CM2-6.....	1/8" X 6"
CMC5-CG....	3/16" X 5"
CMC6-CG....	3/16" X 6"
CM4-CG.....	1/4" X 4-1/2"
CM6-CGC....	1/4" X 6"

- Comply with ASTM F1505 and IEC 60900 Standards and help meet the requirements of OSHA 1910.331-335, NFPA 70E®, and CSA-Z462
- Tested to 10,000 VAC and Rated for 1,000 VAC when working on or around energized parts
- Slender Shape at Tip
- Cushion Grip (CG) handle for greater comfort and torque
- Internal Flanges in handle provide solid, twist-resistant blade



CM6-CGC



PN	DESC
C516-6CG.....	5/16" X 6"
CM516-6CG...	5/16" X 6"
C38-6CG.....	3/8" X 6"

Nut Drivers

PN	DESC
CP1-3-CG...#1	X 3"
CP1-5CG...#1	X 5"
CP2-4CG...#2	X 4"
CP2-6CG...#2	X 6"
CP3-6CG...#3	X 6"

PN	DESC
CR1-6CG....#1	X 6"
CR2-6CG...#2	X 6"
CR3-6CG...#3	X 6"

PN	DESC
CND316-CG3...	3/16" X 3"
CND316-CG.....	3/16" X 6"
CND140-CG3...	1/4" X 3"
CND140-CG.....	1/4" X 6"
CND516-CG3...	5/16" X 3"
CND516-CG.....	5/16" X 6"
CND1132-CG3..	11/32" X 3"
CND1132-CG.....	11/32" X 6"
CND380-CG3..	3/8" X 3"
CND380-CG....	3/8" X 6"
CND716-CG3....	7/16" X 3"
CND716-CG.....	7/16" X 6"
CND120-CG3...	1/2" X 3"
CND120-CG.....	1/2" X 6"
CND916-CG3...	9/16" X 3"
CND916-CG.....	9/16" X 6"
CND580-CG....	5/8" X 6"



CR1-6CG



CP2-4CG



CND916-CG



CM2-3



CMTS-6

Magnetic Tip Multi-Bit Drivers

PN	DESC
CMTS-6.....	6" Shaft, 3/16" & 1/4" Cabinet, #1, #2 & #3 Phillips
CMTS-6CA..	6" Shaft, 3/16" & 1/4" Cabinet, #2 & #3 Phillips, #2 Robertson



Sets / Rolls

TR-5CSD

Composite Cabinet Tip Screwdrivers - 3/16" X 6", 1/4" X 6", 3/8" X 6"
 Composite Phillips Tip Screwdrivers - #2 X 6", #3 X 6"
 Driver Roll Pouch 6

TR-6SD-C

Composite Cabinet Tip Screwdrivers - 3/16" X 5", 3/16" X 6", 1/4" X 6"
 Composite Mechanics Tip Screwdriver - 5/16" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 3", #2 X 4"
 Driver Roll Pouch 6

TR-6CSD

Composite Cabinet Tip Screwdrivers - 1/8" X 6", 3/16" X 6", 1/4" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 5", #2 X 6", #3 X 6"
 Driver Roll Pouch 6

TR-6SD-CSO

Composite Cabinet Tip Screwdrivers - 3/16" X 6", 1/4" X 6"
 Composite Mechanics Tip Screwdriver - 5/16" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 5", #2 X 6", #3 X 6"
 Driver Roll Pouch 6

TR-8SD-C

Composite Cabinet Tip Screwdrivers - 3/16" X 5", 3/16" X 6", 1/4" X 4-1/2", 1/4" X 6"
 Composite Mechanics Tip Screwdriver - 5/16" X 6", 3/8" X 6"
 Composite Phillips Tip Screwdrivers - #1 X 3", #2 X 4"
 Driver Roll Pouch 8

TR-6NDXL-C

6" Composite Nut Drivers - 3/16", 1/4", 5/16", 3/8", 7/16", 1/2"
 Driver Roll Pouch 6

TR-8CND

6" Composite Nut Drivers - 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16"
 Driver Roll Pouch 8

TR-8NDXL-C

6" Composite Nut Drivers: 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2"
 Composite Holding Nut Starter: 5/16" X 8"
 Driver Roll Pouch 8



Holding Screw and Nut Starters


- Spring-Loaded Design allows for easy operation while wearing insulating gloves
- Slender Design for tight area access and storage
- Includes opposing end magnet for retrieval
- Available in multiple sizes and bit tip configurations

PN _____ DESC _____
 CD3-8.....8" Flat Tip
 CD11-8..... 8" Phillips Tip
 CDNS-8...8" Nut Starter



CD11-8

Fuse Pullers



PFP-1

PN _____ DESC _____
 PFP-0..... 5" Fuse Puller without Guards
 PFP-0G.....7-1/4" Fuse Puller with Guards
 PFP-1.....7-1/2" Fuse Puller (without Guards)
 PFP-2G.....5" Fuse Puller with Guards
 PFP-3.....11-3/4" Fuse Puller without Guards

Non-Conductive Pliers

- Non-conductive tool
- Completely concealed pivot pin (only steel component)
- Slender Jaws for entry to tight areas

PN _____ DESC _____
 PK100....7" Fiberglass Reinforced Plastic



PK100



Measuring Tape

PN _____ DESC _____
 CTM-33... 33' Fully Non-Conductive
 Fiberglass Measuring Tape