

# Specifications



Photo is representative

## Eaton CDR6044

Eaton Crouse-Hinds series PowerMate CDR receptacle, 60A, Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

### General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CDR receptacle
CATALOG NUMBER	CDR6044
UPC	662276277007
PRODUCT LENGTH/DEPTH	4.25 in
PRODUCT HEIGHT	4.5 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	2.2 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

## Resources

3D CAD DRAWING PACKAGE	<a href="#">Eaton Crouse-Hinds CDR6044 3D drawing</a>
BROCHURES	<a href="#">PowerMate Drilling Pin and Sleeve Devices brochure</a>
CATALOGS	<a href="#">PowerMate Drilling Pin and Sleeve Devices catalog page</a>
CERTIFICATION REPORTS	<a href="#">PowerMate Drilling Pin and Sleeve Devices UL certification (Receptacles)</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing</a> <a href="#">IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">PowerMate Connectors</a> <a href="#">Eaton Specification Sheet - CDR6044</a>

## Product specifications

AMPERAGE RATING	60A
GROUNDING TYPE	Style 1
CONFIGURATION	Four-wire, four-pole
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.