

Eaton CE15ENS3AB

Catalog Number: CE15ENS3AB

Eaton XT IEC contactor, 25A, 110-120 Vac, 50-60 Hz, 1NO, 25A, Frame E, 50-60 Hz, 2 hp, Side, Three-pole, Non-reversing, No overload relay, Freedom, Contactor



Photo is representative

General specifications

Product Name

Eaton XT IEC contactor

Catalog Number

CE15ENS3AB

UPC

782113779010

Product Length/Depth

3.25 in

Product Height

2.96 in

Product Width

1.8 in

Product Weight

1.01 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

ISO 9000

DIN VDE 0600

Certifications

UL Listed

IEC Rated

CSA Certified

Catalog Notes

No enclosure

defaultTaxonomyAttributeLabel

Amperage Rating

25A

HP rating - max

2 hp

Number Of Poles

Three-pole

Type

Contactors

Frequency rating

50-60 Hz

Frame size

E

Coil voltage

110-120 Vac, 50-60 Hz

Contact configuration

1 NO

Continuous ampere rating

25 A

Relay

No overload relay

Series

Freedom

Operation

Non-reversing

Mounting method

Side

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

[Motor Starters and Contactors — Low Voltage Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - CE15ENS3AB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)