



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CF26DTEIN830ECO Fluor LMP

Sylvania-Ledvance

Catalog Number	CF26DTEIN830ECO
Manufacturer	Sylvania-Ledvance
Description	Dulux 26W Triple Compact Fluorescent Amalgam Lamp With 4 Pin Base, 3000K Color Temperature, 82 Cri, For Use With Electronic and Dimming Ballasts, Ecologic
Weight per unit	0.1800 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

amperage rating	Ballast Dependent
average life	16000
Base	GX24Q-3;GX24q-3
Lamp Type	DULUX T/E
lumens	1,746
Shape	T4
start type	ELECTRONIC RAPID START
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	26

Material, Color, and Finish

color rendering index (cri)	82
color temperature	3000
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.5000000000000000
Length	5

Descriptions

Description	FLUOR LMP
extra long description	SYL CF26DT/E/IN/830/ECO/20880 CF26D
Long Description	DULUX 26W triple compact fluorescent amalgam lamp with 4 pin base, 3000K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC
Product Type	CF26DTEIN830ECO 50/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135208805
Manufacturers Part Number	CF26DT/E/IN/830/ECO/20880
UPC	046135208805



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent

Packaging

Carton	1
Package	50
Weight Per each	0.18

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------