

# Eaton CGB398

Catalog Number: CGB398

Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.875-1.000", Non-armoured and tray cable, Non-armoured, Steel, General purpose, 1" NPT, Form D

## General specifications



|   |                |
|---|----------------|
| Product Name                              | Catalog Number |
| Eaton Crouse-Hinds series CGB cable gland | CGB398         |
|   | UPC            |
|   | 782274134604   |
| Product Length/Depth                      | Product Height |
| 3.21 in                                   | 2.25 in        |
| Product Width                             | Product Weight |
| 2.25 in                                   | 1.1 lb         |

## Product specifications

### Gland type

Non-armoured

### Thread Size

1"

### NEMA Rating

3R

4

### Area classification

Ordinary/Non-Hazardous Locations

### Cable range (min/max)

0.875-1.000"

### Material

Steel

### Cable type

Tray cable

Non-armoured

### Thread type

NPT

### Standards type

NEC/CEC

### Protection type

General purpose

## Resources

### Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

### Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

### Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

### Installation instructions

[IF 1826 - CGB, CGD and CGE Connectors](#)

[IF 513A - CG Fittings Installation](#)

### Specifications and datasheets

[Eaton Specification Sheet - CGB398](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)