

# Eaton CGB599

Catalog Number: CGB599

Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 1.000-1.188", Non-armoured and tray cable, Non-armoured, Steel, General purpose, 1-1/2" NPT

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series CGB cable gland	CGB599
	UPC
	782274135601
Product Length/Depth	Product Height
3.27 in	2.25 in
Product Width	Product Weight
2.25 in	1.19 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3R

4

## Product specifications

### Protection type

General purpose

### Cable type

Non-armoured

Tray cable

### Gland type

Non-armoured

### Thread Size

1-1/2"

### Thread type

NPT

### Cable range (min/max)

1.000-1.188"

### Material

Steel

## Resources

### Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

### Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

### Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

### Installation instructions

[IF 1826 - CGB, CGD and CGE Connectors](#)

[IF 513A - CG Fittings Installation](#)

### Specifications and datasheets

[Eaton Specification Sheet - CGB599](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)