



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH10EGEN3060 Emergency Generator Panel 10 Circuit Indoor

Eaton Corp

Catalog Number	CH10EGEN3060
Manufacturer	Eaton Corp
Description	Eaton CH Transfer Switch Panel, Emergency Generator Panel, For Gen/Tran 302110-20 and Emergen 10-7500, 60A Main, 30A Emergency, 10 Circuits, Nema 1 Enclosure, 7.5 KW, (6) Single-Pole 15A, (2) Single-Pole 20a
Weight per unit	25.0 (lbs/each)
Product Category	Other Generators

Features

media	Yes
-------	-----

Dimensions and Weight

Depth	13
Height	11.2
Width	4.4

Descriptions

Description	EMERGENCY GENERATOR PANEL 10 CIRCUIT INDOOR
extra long description	ETN CH10EGEN3060 EMER GENERATOR PAN
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH transfer switch panel, Emergency generator panel, For Gen/Tran 302110-20 and EmerGen 10-7500, 60A main, 30A emergency, 10 circuits, NEMA 1 enclosure, 7.5 kW, (6) single-pole 15A, (2) single-pole 20A
Product Type	Emer Generator Panel, 10 CKT, Indoor
Special Features	Used with Gen/Tran 302110-20 and EmerGen 10-7500

Manufacturer Information

Brand	Eaton
GTIN	00782114556962
Manufacturers Part Number	CH10EGEN3060
UPC	782114556962

Taxonomies, Classifications, and Categories

Category Description	TRANSFER SWITCHES
Type	Transfer switch panel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	25

Uses, Certifications, and Standards

Application	Other
standard	UL 67,UL 1008