

Eaton CH18L3125C

Catalog Number: CH18L3125C

Eaton CH main lug loadcenter, Main lug only, 125 A, C, Copper, NEMA 1, Metallic, Top/bottom, CH, 18 Circuits, 18 Spaces, Four-wire, Three-phase, #1-4/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH18L3125C
UPC	Product Length/Depth
782113097534	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
25 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Furnished with hub closure plates.

defaultTaxonomyAttributeLabel

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Feed type

Top/bottom

Main circuit breaker

CH

Number of circuits

18

Number of spaces

18

Phase

Three-phase

Wire size

#1-4/0 AWG

Box size

C

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

35 kAIC

Number of wires

4

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 3 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH18L3125C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)