

Eaton CH2100ST

Catalog Number: CH2100ST

Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 100 A, 10 kAIC, Two-pole, 120/240V, CH, Common breaker trip, #10-1/0 AWG Cu/Al, CH, Type CH Loadcenters, Shunt trip included

General specifications



Photo is representative

Product Name

Eaton CH thermal magnetic circuit breaker

Catalog Number

CH2100ST

UPC

782113364285

Product Length/Depth

3.5 in

Product Height

4.4 in

Product Width

3.5 in

Product Weight

0.9 lb

Warranty

Limited lifetime residential, 1 year commercial

Certifications

UL 489

Catalog Notes

Two-Pole 120/240V Common Trip
Requires Two 3/4-Inch Spaces

defaultTaxonomyAttributeLabel

Type

Type CH 3/4-Inch standard circuit breaker

Special features

Shunt Trip

Amperage Rating

100 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Shunt trip

Included

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CH

Wire size

#10-1/0 AWG Cu/Al

Number of poles

Two-pole

Resources

Brochures

[Type CH Circuit Breakers and Loadcenters](#)

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH2100ST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia