



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH230GFT Type BR 5 Ma GFI BRKR 30A/2 Pole 120/240V 10K Self

Eaton Corp

Catalog Number	CH230GFT
Manufacturer	Eaton Corp
Description	Ground Fault Circuit Breaker, 30 A, Common Tripping Mechanism, Line and Load Lug Terminal, Plug-On, #14 to #4 Awg Wire Size, 2 In Overall Height, 4.5 In Overall Length, 2.75 In Overall Width, 0.8 LB
Weight per unit	0.8000 (lbs/each)
Product Category	In Circuit Breakers

Features

amperage rating	30 A
connection	Plug-on
dimensions	4.5000 IN X 2.7500 IN X 2.0000 IN
Poles	2
Trip Type	Common
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR 5 MA GFI BRKR 30A/2 POLE 120/240V 10K SELF
extra long description	ETN CH230GFT BR 5 MA GFI 30A/2 POLE
Special Features	Ground Fault Self Test

Manufacturer Information

Brand	Eaton
GTIN	00786676025645
UPC	786676025645

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Packaging

Carton	1
Package	10
Weight Per each	0.8

Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper ConvergedOtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489